



Pass and Seymour  
**15A 125V Clock Hanger Recessed Single Receptacle with Smooth Wall Plate, Black**  
Part No. S3713BK



Clock Hanger Recessed Receptacle with Smooth Wall Plate 15A, 125V, Gray

## Features & Benefits

Single recessed receptacle. Available in 'TP' series, extra 3/16 inch width and height than Standard size plates: and 'TPJ' series, extra 3/16 inch width and height than Junior-Jumbo size plates.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007687811	Country Of Origin	Mexico
Number of Receptacles	1	Application Sector	Commercial, Residential
Standard	UL 498	Type	Outlet

### Dimensions

Product Width US	2.74 in	Product Depth US	1.88 in
Product Height US	4.478 in		

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

### Technical Information

Number of Wires	3	Amperage	15 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG

---

Indoor/Outdoor

Indoor

---