



Pass and Seymour
15A 125V Clock Hanger Recessed Single Receptacle with Smooth Wall Plate, Ivory
Part No. S3713I



Clock Hanger Recessed Receptacle with Smooth Wall Plate 15A, 125V, Gray

Features & Benefits

Single recessed receptacle. Available in 'TP' series, extra 3/16 inch width and height than Standard size plates: and 'TPJ' series, extra 3/16 inch width and height than Junior-Jumbo size plates.

Specifications

General Info

| | | | |
|-----------------------|----------------|--------------------|-------------------------|
| Product Line | Pass & Seymour | Color | Ivory |
| UPC Number | 785007687804 | Country Of Origin | Mexico |
| Number of Receptacles | 1 | Application Sector | Commercial, Residential |
| Standard | UL 498 | Type | Outlet |

Dimensions

| | | | |
|-------------------|----------|------------------|---------|
| Product Width US | 2.74 in | Product Depth US | 1.88 in |
| Product Height US | 4.478 in | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140596 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Technical Information

| | | | |
|------------|-------------|-----------------|-------------|
| Connection | Wire Ground | Number of Wires | 3 |
| Amperage | 15 A | Number of Poles | Double Pole |
| Wire Size | 4 AWG | Indoor/Outdoor | Indoor |