



Pass and Seymour  
**15A 125V Tamper-Resistant Clock Hanger Recessed Single Receptacle with Smooth Wall Plate, Gray**  
Part No. S3713TRGRY



Tamper-Resistant Clock Hanger Recessed Receptacle with Smooth Wall Plate 15A, 125V. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

## Features & Benefits

Single recessed receptacle. Available in 'TP' series, extra 3/16 inch width and height than Standard size plates: and 'TPJ' series, extra 3/16 inch width and height than Junior-Jumbo size plates.

## Specifications

### General Info

|                       |                         |                   |                  |
|-----------------------|-------------------------|-------------------|------------------|
| Product Line          | Pass & Seymour          | Color             | Gray             |
| UPC Number            | 785007197587            | Country Of Origin | Mexico           |
| Number of Receptacles | 1                       | Outlet Type       | Tamper-Resistant |
| Application Sector    | Commercial, Residential | Standard          | UL 498           |
| Type                  | Outlet                  |                   |                  |

### Dimensions

|                   |          |                  |         |
|-------------------|----------|------------------|---------|
| Product Width US  | 2.74 in  | Product Depth US | 1.88 in |
| Product Height US | 4.478 in |                  |         |

### Listing Agencies / 3rd Party Agencies

|              |     |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

### Technical Information

|                     |      |                 |             |
|---------------------|------|-----------------|-------------|
| Is Tamper-Resistant | Yes  | Number of Wires | 3           |
| Amperage            | 15 A | Number of Poles | Double Pole |

|           |             |                |        |
|-----------|-------------|----------------|--------|
| Wire Size | 14 - 12 AWG | Indoor/Outdoor | Indoor |
|-----------|-------------|----------------|--------|