



Pass and Seymour
Clock Hanger Receptacles, Recessed with Stainless Steel Wall Plate, 15A, 125V
Part No. S3733SS



Clock Hanger Receptacles, Recessed with Stainless Steel Wall Plate, 15A, 125A

Features & Benefits

Single recessed receptacle.

Stainless steel: wall plate.

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	United States
Application Sector	Commercial	Standard	UL 498

Dimensions

Product Width US	2.74 in	Product Depth US	1.88 in
Product Height US	4.478 in		

Technical Information

Number of Wires	3	Amperage	15 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Voltage	115.0 V		