



Pass and Seymour  
Power Outlet Receptacle Openings, Two Gang, Chrome  
Part No. S3863C



TwoGang Power Outlet Receptacle Opening, 2.4688 hole for 2.375 diameter device -4 mtg. holes, Smooth Metal.

## Features & Benefits

Chrome: .040" thick.

Lacquered to prevent corrosion.

Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide.

Variety of special plated finishes.

Can be silk-screened or engraved, and custom punched with over 300 opening styles.

70% copper, 30% zinc alloy gives warm, appealing finish to modern decor as well as retrofit applications.

Constructed of corrosion-resistant stainless steel, brass, aluminum, chrome, brushed bronze, or galvanized steel.

Packaged in protective film, with finish-matching screws.

Paintable to match plastic plates.

## Specifications

### General Info

Product Line	Pass & Seymour	Country Of Origin	United States
Application Sector	Residential/Commercial		

### Dimensions

Product Width US	4.56 in	Product Depth US	0.2 in
Product Height US	4.5 in		

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

---

## Technical Information

---

Cutout	Power Outlet	Thickness	0.04 in
--------	--------------	-----------	---------

---

Number of Gangs	2
-----------------	---

---