




Smooth Metal Wall Plate, 3-Gang Decorator, Polished Brass



## Features & Benefits

Polished Brass: .040" thick.

Lacquered to prevent corrosion.

Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide.

Variety of special plated finishes.

Can be silk-screened or engraved, and custom punched with over 300 opening styles.

70% copper, 30% zinc alloy gives warm, appealing finish to modern decor as well as retrofit applications.

Constructed of corrosion-resistant stainless steel, brass, aluminum, chrome, brushed bronze, or galvanized steel.

Packaged in protective film, with finish-matching screws.

Paintable to match plastic plates.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Brass
Finish	Metallic	UPC Number	785007137712
Country Of Origin	United States	Wall Plate Size	Standard Size
Wall Plate Type	Toggle Switch	Application Sector	Commercial, Residential
Warranty Type	1-Year Limited Warranty	Type	Wall Plate

### Dimensions

Product Width US	6.375 in	Product Depth US	0.2 in
Product Height US	4.5 in		

### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes
------------	-----	--------------	-----

### Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Thickness	0.04 in	Number of Gangs	3
Indoor/Outdoor	Indoor	Mounting Type	Box Mounted
Orientation	Vertical		