



Pass and Seymour
2-Gang Chrome Wall Plate, 2 Duplex Receptacle Openings
Part No. SB82CH



Smooth Metal Wall Plate 2-Gang Duplex Chrome

Features & Benefits

Chrome: .040" thick.

Lacquered to prevent corrosion.

Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide.

Variety of special plated finishes.

Can be silk-screened or engraved, and custom punched with over 300 opening styles.

70% copper, 30% zinc alloy gives warm, appealing finish to modern decor as well as retrofit applications.

Constructed of corrosion-resistant stainless steel, brass, aluminum, chrome, brushed bronze, or galvanized steel.

Packaged in protective film, with finish-matching screws.

Paintable to match plastic plates.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Chrome
Finish	Metallic	UPC Number	785007138443
Country Of Origin	United States	Wall Plate Size	Standard Size
Wall Plate Type	Duplex Receptacle	Application Sector	Commercial, Residential
Warranty Type	1-Year Limited Warranty	Type	Wall Plate

Dimensions

Product Width US	4.56 in	Product Depth US	0.2 in
Product Height US	4.5 in		
Listing Agencies / 3rd Party Agencies			
CSA Listed	Yes	cULus Listed	Yes
Additional Information			
Product Environmental Profile	Yes		
Technical Information			
Thickness	0.04 in	Number of Gangs	2
Indoor/Outdoor	Indoor	Mounting Type	Strap Mounted
Orientation	Vertical		