



Pass and Seymour
Double Weave, Standard Length, Closed Mesh, Offset Eye
Part No. SCK1501



Double Weave, Standard Length, Closed Mesh, Offset Eye. Cable Diameter - 1.500-1.740-inch, Mesh Length - 18-inch, Break Strength - 7,400 lbs.

Features & Benefits

Slack grips are reusable grips used for pulling slack in underground cable preparatory to final placement.

They may also be used for cable removal. Slack grips feature an offset eye for easy attachment to the pulling line.

Mesh Length: 18

Specifications

General Info

| | | | |
|--------------|---|--------------------|------------|
| Product Line | Pass & Seymour | Country Of Origin | Mexico |
| Construction | Support and Strain Relief Grips, Various Types of Pulling | Application Sector | Industrial |
| Standard | UL/CSA Approval (consult factory) | | |

Technical Information

| | | | |
|---------------------|-------------------------------|---------------------|--|
| Maximum Cable Range | 1.5 in | Minimum Cable Range | 1.74 in |
| Capacity | Various Cable Diameter Ranges | Mounting | Consult the Factory for Mounting Recommendations |
| Load | Approx. Break Strength: 7400 | | |