



Pass and Seymour
Combination Openings, 1 Toggle Switch and 2 Decorator, Three Gang, Ivory
Part No. SP1262I



Combination Wall Plate, 1 Toggle Switch and 2 Decorator, 3-Gang

Features & Benefits

Molded of non-combustible mar-proof material.

Available in 'SP' series in Standard, Junior-Jumbo, and Jumbo sizes.

Seven standard colors available -- Ivory, White, Brown, Gray, Black, Red, and Light Almond.

Individually wrapped with color-matching screws.

Resistant to discoloration, grease, oil, solvent, and moisture.

Nominal thickness, .070 inch.

Specifications

General Info

| | | | |
|-------------------|---------------------------------------|--------------------|---------------------------|
| Product Line | Pass & Seymour | Color | Ivory |
| Finish | Matte | UPC Number | 785007681840 |
| Country Of Origin | Mexico | Features | Combination |
| Wall Plate Type | Combination, Decorator, Toggle Switch | Application Sector | Commercial, Residential |
| Standard | CSA, UL514 | Warranty Type | Limited Lifetime Warranty |
| Type | Wall Plate | | |

Dimensions

| | | | |
|-------------------|----------|------------------|--------|
| Product Width US | 6.375 in | Product Depth US | 0.2 in |
| Product Height US | 4.5 in | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|------------|-----|-----------------|-------|
| CSA Listed | Yes | CSA File Number | 17695 |
|------------|-----|-----------------|-------|

Additional Information

Product Environmental Profile Yes

Technical Information

| | | | |
|-----------------|----------------------|-------------|---------------|
| Cutout | Toggle and Decorator | Thickness | 0.07 in |
| Number of Gangs | 3 | Wire Size | #14 - #10 AWG |
| Indoor/Outdoor | Indoor | Orientation | Horizontal |
