



Pass and Seymour  
Combination Openings, 1 Telephone and 1 Duplex Receptacle, Two Gang, White  
Part No. SP128W



Double gang with single phone and single duplex combination. Has 13/32 in and 5/8-inch double knockout. Smooth Thermoset. .

## Features & Benefits

Constructed of corrosion-resistant stainless steel, brass, aluminum, chrome, brushed bronze, or galvanized steel.

Packaged in protective film, with finish-matching screws.

Paintable to match plastic plates.

Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide.

Variety of special plated finishes.

Can be silk-screened or engraved, and custom punched with over 300 opening styles.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Country Of Origin	Mexico	Wall Plate Type	Coaxial, Combination, Outlet
Application Sector	Residential/Commercial	Standard	CSA, UL514

### Dimensions

Product Width US	4.56 in	Product Depth US	0.2 in
Product Height US	4.5 in		

### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	17695
------------	-----	-----------------	-------

### Technical Information

Cutout	Telephone and Receptacle	Thickness	0.07 in
Number of Gangs	2	Mounting Type	Exposed Screws