



Single-Gang, Single telephone or cable outlet 13/32-inch hole. Strap mounted with adjustable yoke. One #340 yoke. Smooth thermoset. .

Features & Benefits

| | |
|---|--|
| Molded of non-combustible mar-proof material. | Available in 'SP' series in Standard, Junior-Jumbo, and Jumbo sizes. |
| Seven standard colors available -- Ivory, White, Brown, Gray, Black, Red, and Light Almond. | Individually wrapped with color-matching screws. |
| Resistant to discoloration, grease, oil, solvent, and moisture. | Nominal thickness, .070 inch. |

Specifications

| | | | |
|---------------------------------------|-------------------------|--------------------------|---------------------------|
| General Info | | | |
| Product Line | Pass & Seymour | Color | Red |
| Finish | Matte | UPC Number | 785007186260 |
| Country Of Origin | Mexico | Construction | Plastic |
| Wall Plate Size | Standard Size | Wall Plate Type | Coaxial, Round, Telephone |
| Application Sector | Commercial, Residential | Standard | CSA, UL514 |
| Warranty Type | 1-Year Limited Warranty | Type | Wall Plate |
| Dimensions | | | |
| Product Width US | 2.75 in | Product Depth US | 0.2 in |
| Product Height US | 4.5 in | Circular Outlet Diameter | 0.53 mm |
| Listing Agencies / 3rd Party Agencies | | | |
| CSA Listed | Yes | CSA File Number | 17695 |
| Additional Information | | | |
| Product Environmental Profile | Yes | | |

Technical Information

| | | | |
|----------------|----------|-----------------|---------------|
| Thickness | 0.07 in | Number of Gangs | 1 |
| Indoor/Outdoor | Indoor | Mounting Type | Strap Mounted |
| Orientation | Vertical | | |