



**Pass and Seymour**  
**Combination Openings, 1 Blank and 1 Duplex Receptacle, Two Gang, Ivory**  
Part No. SP138I



Combination Wall Plate, 1 Blank and 1 Duplex Receptacle, 2-Gang

## Features & Benefits

Molded of non-combustible mar-proof material.

Seven standard colors available -- Ivory, White, Brown, Gray, Black, Red, and Light Almond.

Resistant to discoloration, grease, oil, solvent, and moisture.

Available in 'SP' series in Standard, Junior-Jumbo, and Jumbo sizes.

Individually wrapped with color-matching screws.

Nominal thickness, .070 inch.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Ivory
Country Of Origin	Mexico	Wall Plate Type	Blank, Combination, Outlet
Application Sector	Residential/Commercial	Standard	CSA, UL514

### Dimensions

Product Width US	4.56 in	Product Depth US	0.2 in
Product Height US	4.5 in		

### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	17695
------------	-----	-----------------	-------

---

## Technical Information

---

Cutout	Blank and Receptacle	Thickness	0.07 in
Number of Gangs	2	Mounting Type	Exposed Screws

---