



Pass and Seymour
3-Gang Thermoset Wall Plate, Blank, Box Mounted, Ivory
Part No. SP331



Smooth Wall Plate 3-Gang Blank Box Mount

Features & Benefits

Molded of non-combustible mar-proof material.

Seven standard colors available -- Ivory, White, Brown, Gray, Black, Red, and Light Almond.

Resistant to discoloration, grease, oil, solvent, and moisture.

Available in 'SP' series in Standard, Junior-Jumbo, and Jumbo sizes.

Individually wrapped with color-matching screws.

Nominal thickness, .070 inch.

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Finish	Matte	UPC Number	785007186949
Country Of Origin	Mexico	Construction	Plastic
Wall Plate Size	Standard Size	Wall Plate Type	Blank
Application Sector	Commercial, Residential	Standard	CSA, UL514
Warranty Type	1-Year Limited Warranty	Type	Wall Plate

Dimensions

Product Width US	6.375 in	Product Depth US	0.2 in
Product Height US	4.5 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	17695
------------	-----	-----------------	-------

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Thickness	0.07 in	Number of Gangs	3
-----------	---------	-----------------	---

Indoor/Outdoor	Indoor	Mounting Type	Box Mounted
----------------	--------	---------------	-------------

Orientation	Vertical
-------------	----------
