



**Pass and Seymour
Combination Openings, 3 Toggle Switch and 1 Duplex Receptacle, Four Gang, Brown**
Part No. SP38

□ This 4-gang wall plate provides opening for 3-toggle switches and 1-duplex receptacle

Features & Benefits

Molded of non-combustible mar-proof material.	Available in 'TP' series, extra 3/16 inch width and height than Standard size plates: and 'TPJ' series, extra 3/16 inch width and height than Junior-Jumbo size plates.
Seven standard colors available -- Ivory, White, Brown, Gray, Black, Red, and Light Almond.	Individually wrapped with color-matching screws.
Resistant to discoloration, grease, oil, solvent, and moisture.	Nominal thickness, .070 inch.

Specifications

General Info

Product Line	Pass & Seymour	Color	Brown
Country Of Origin	Mexico	Wall Plate Type	Combination, Dimmer/Switch, Outlet
Application Sector	Residential/Commercial	Standard	CSA, UL514

Dimensions

Product Width US	8.125 in	Product Depth US	0.2 in
Product Height US	4.5 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	17695
------------	-----	-----------------	-------

Technical Information

Cutout	Toggle and Receptacle	Thickness	0.07 in
Number of Gangs	4	Mounting Type	Exposed Screws