



Pass and Seymour
4-Gang Thermoset Wall Plate, Blank, Box Mounted, Ivory
Part No. SP43I



Smooth Wall Plate, 4-Gang Blank, Box Mount

Features & Benefits

Molded of non-combustible mar-proof material.

Available in 'SP' series in Standard, Junior-Jumbo, and Jumbo sizes.

Seven standard colors available -- Ivory, White, Brown, Gray, Black, Red, and Light Almond.

Individually wrapped with color-matching screws.

Resistant to discoloration, grease, oil, solvent, and moisture.

Nominal thickness, .070 inch.

Specifications

General Info

| | | | |
|--------------------|-------------------------|-----------------|--------------|
| Product Line | Pass & Seymour | Color | Ivory |
| Finish | Matte | UPC Number | 785007187243 |
| Country Of Origin | Mexico | Construction | Plastic |
| Wall Plate Size | Standard Size | Wall Plate Type | Blank |
| Application Sector | Commercial, Residential | Standard | CSA, UL514 |
| Warranty Type | 1-Year Limited Warranty | Type | Wall Plate |

Dimensions

| | | | |
|-------------------|----------|------------------|--------|
| Product Width US | 8.125 in | Product Depth US | 0.2 in |
| Product Height US | 4.5 in | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|------------|-----|-----------------|-------|
| CSA Listed | Yes | CSA File Number | 17695 |
|------------|-----|-----------------|-------|

Additional Information

| | |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

Technical Information

| | | | |
|-----------|---------|-----------------|---|
| Thickness | 0.07 in | Number of Gangs | 4 |
|-----------|---------|-----------------|---|

| | | | |
|----------------|--------|---------------|-------------|
| Indoor/Outdoor | Indoor | Mounting Type | Box Mounted |
|----------------|--------|---------------|-------------|

| | |
|-------------|----------|
| Orientation | Vertical |
|-------------|----------|