



Pass and Seymour
Power Outlet Receptacle Openings, Two Gang, Brown
Part No. SP703



TwoGang Power Outlet Receptacle Opening, 2.1563 hole for 2.125 diameter device -4 mtg. holes,BrownThermoset.

Features & Benefits

Molded of non-combustible mar-proof material.

Available in 'SP' series in Standard, Junior-Jumbo, and Jumbo sizes.

Seven standard colors available -- Ivory, White, Brown, Gray, Black, Red, and Light Almond.

Individually wrapped with color-matching screws.

Resistant to discoloration, grease, oil, solvent, and moisture.

Nominal thickness, .070 inch.

Specifications

General Info

Product Line	Pass & Seymour	Color	Brown
Finish	Matte	UPC Number	785007189209
Country Of Origin	Mexico	Wall Plate Type	Outlet, Round
Application Sector	Commercial, Residential	Standard	CSA, UL514
Warranty Type	Limited Lifetime Warranty	Type	Wall Plate

Dimensions

Product Width US	4.56 in	Product Depth US	0.2 in
Product Height US	4.5 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	17695
------------	-----	-----------------	-------

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Cutout	Power Outlet	Thickness	0.07 in
Number of Gangs	2	Indoor/Outdoor	Indoor
Mounting Type	Exposed Screws	Orientation	Horizontal