

OneGang Power Outlet Receptacle Opening, 1.5938 hole for 1.5625 diameter device -2 mtg. holes,Brown Thermoset.



Features & Benefits

Molded of non-combustible mar-proof material.

Available in 'SP' series in Standard, Junior-Jumbo, and Jumbo sizes.

Seven standard colors available -- Ivory, White, Brown, Gray, Black, Red, and Light Almond.

Individually wrapped with color-matching screws.

Resistant to discoloration, grease, oil, solvent, and moisture.

Nominal thickness, .070 inch.

Specifications

General Info

Product Line	Pass & Seymour	Color	Brown
Finish	Matte	UPC Number	785007189308
Country Of Origin	Mexico	Construction	Plastic
Wall Plate Size	Standard Size	Wall Plate Type	Outlet, Round
Application Sector	Commercial, Residential	Standard	CSA, UL514
Warranty Type	1-Year Limited Warranty	Type	Wall Plate

Dimensions

Product Width US	2.75 in	Product Depth US	0.2 in
Product Height US	4.5 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	17695
------------	-----	-----------------	-------

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Thickness	0.07 in	Number of Gangs	1
Indoor/Outdoor	Indoor	Mounting Type	Box Mounted
Orientation	Vertical		