



OneGang Power Outlet Receptacle Opening, 1.5938 hole for 1.5625 diameter device -2 mtg. holes,Brown Thermoset.

Features & Benefits

Molded of non-combustible mar-proof material.	Available in 'SP' series in Standard, Junior-Jumbo, and Jumbo sizes.
Seven standard colors available -- Ivory, White, Brown, Gray, Black, Red, and Light Almond.	Individually wrapped with color-matching screws.
Resistant to discoloration, grease, oil, solvent, and moisture.	Nominal thickness, .070 inch.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Country Of Origin	Mexico	Wall Plate Type	Single Outlet
Application Sector	Residential/Commercial	Standard	CSA, UL514

Dimensions

Product Width US	2.75 in	Product Depth US	0.2 in
Product Height US	4.5 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	17695
------------	-----	-----------------	-------

Technical Information

Cutout	Power Outlet	Thickness	0.07 in
Number of Gangs	1	Mounting Type	Exposed Screws
