



Pass and Seymour
4-Gang Thermoset Wall Plate, 4 Duplex Receptacle Openings, White
Part No. SP84W

Duplex Receptacle Wall Plate, 4-Gang



Features & Benefits

Molded of non-combustible mar-proof material.

Available in 'SP' series in Standard, Junior-Jumbo, and Jumbo sizes.

Seven standard colors available -- Ivory, White, Brown, Gray, Black, Red, and Light Almond.

Individually wrapped with color-matching screws.

Resistant to discoloration, grease, oil, solvent, and moisture.

Nominal thickness, .070 inch.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

| | | | |
|--------------------|-------------------------|-----------------|-------------------|
| Product Line | Pass & Seymour | Color | White |
| Finish | Matte | UPC Number | 785007187786 |
| Country Of Origin | Mexico | Construction | Plastic |
| Wall Plate Size | Standard Size | Wall Plate Type | Duplex Receptacle |
| Application Sector | Commercial, Residential | Standard | CSA, UL514 |
| Warranty Type | 1-Year Limited Warranty | Type | Wall Plate |

Dimensions

| | | | |
|-------------------|----------|------------------|--------|
| Product Width US | 8.125 in | Product Depth US | 0.2 in |
| Product Height US | 4.5 in | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|------------|-----|-----------------|-------|
| CSA Listed | Yes | CSA File Number | 17695 |
|------------|-----|-----------------|-------|

Additional Information

| | |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

Technical Information

| | | | |
|----------------|----------|-----------------|---------------|
| Thickness | 0.07 in | Number of Gangs | 4 |
| Indoor/Outdoor | Indoor | Mounting Type | Strap Mounted |
| Orientation | Vertical | | |
