



Ortronics
TECHCHOICE CAT6A PATCH PANEL, ANGLED 24 PORT
Part No. SPA6AU24



TechChoice Cat6A/10G angled 24-port high density patch panel with multiport modules (6 jacks in a group) and utilizes a recessed angle design for a lower mounted profile. Supplied rear cable management. Circuit isolation and supports the alien crosstalk requirements of IEEE 10G and TIA Category 6a cabling specifications. Panels occupies one rack unit, and measure 19" x 1.75".

Features & Benefits

Recessed design with lower mounted profile: Directs cords more easily to vertical management.

Tested to TIA 568-C Cat6A with SPC6A cords: More transparent mated union resulting in superior performance.

Universally wired 110 termination: Supports T568A and T568B installs.

Cat6A/10 Gig compatible IDC towers: Designed to accept larger Cat6A cable conductors.

Supplied rear cable management: Supports good cabling practices.

High density design: Maximizes rack utilization.

Specifications

General Info

Product Line	Ortronics	Color	Black
UPC Number	662875996767	Country Of Origin	Mexico
Application Sector	Commercial/Industrial	Type	Panel

Dimensions

Product Width US	19.0 in	Product Depth US	6.09 in
Product Height US	1.75 in		

Additional Information

RoHS Conformant	Yes	Product Environmental Profile	Yes
-----------------	-----	-------------------------------	-----