



Smooth Metal Wall Plate, 8-Gang Decorator, 302/304 Stainless Steel Painted

Features & Benefits

- Type 302/304 Stainless Steel, non-magnetic: .032” nominal thickness. Brushed finish.
- This alloy contains 18% chromium and 8% nickel for superior resistance to corrosion.
- Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide.
- Variety of special plated finishes.
- Can be silk-screened or engraved, and custom punched with over 300 opening styles.
- Recommended for use in food processing plants, dairies, chemical plants, and other industrial, institutional, and commercial applications where corrosive atmospheres exist.
- Packaged in protective film, with finish-matching screws.
- Paintable to match plastic plates.

Specifications

General Info			
Product Line	Pass & Seymour	Color	Ivory
Finish	Metallic	UPC Number	785007136937
Country Of Origin	United States	Wall Plate Size	Standard Size
Wall Plate Type	Decorator	Application Sector	Commercial, Residential
Standard	CSA	Warranty Type	1-Year Limited Warranty
Type	Wall Plate		
Dimensions			
Product Width US	15.44 in	Product Depth US	0.2 in
Product Height US	4.5 in		
Listing Agencies / 3rd Party Agencies			
CSA Listed	Yes	cULus Listed	Yes
Additional Information			
Product Environmental Profile	Yes		
Technical Information			
Thickness	0.032 in	Number of Gangs	8
Indoor/Outdoor	Indoor	Mounting Type	Box Mounted

Orientation

Vertical
