



Pass and Seymour  
Two-Gang Wall Plate Single Custom Cutout, 302/304 Stainless Steel  
Part No. SS747



Double gang, Single receptacle cente opening. 302/304 Stainless steel.

## Features & Benefits

Type 302/304 Stainless Steel, non-magnetic: .032"<sup>\*\*\*</sup> nominal thickness. Brushed finish.

This alloy contains 18% chromium and 8% nickel for superior resistance to corrosion.

Recommended for use in food processing plants, dairies, chemical plants, and other industrial, institutional, and commercial applications where corrosive atmospheres exist.

Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide.

Packaged in protective film, with finish-matching screws.

Variety of special plated finishes.

Paintable to match plastic plates.

Can be silk-screened or engraved, and custom punched with over 300 opening styles.

## Specifications

### General Info

Product Line	Pass & Seymour	Country Of Origin	United States
Application Sector	Residential/Commercial	Standard	CSA

### Dimensions

Product Width US	4.56 in	Product Depth US	0.2 in
Product Height US	4.5 in		

### Listing Agencies / 3rd Party Agencies

---

CSA Listed

Yes

cULus Listed

Yes

---

### Technical Information

---

Cutout

Single Receptacle

Thickness

0.032 in

---

Number of Gangs

2

---