



Single-Gang, Single outlet horizontal split wall plate for television or cable lead in. Supplied with #340 yoke, Strap mounted removable 5/8 in ID grommet in 7/8-inch hole. Smooth 302/304 Stainless Steel.

Features & Benefits

Type 302/304 Stainless Steel, non-magnetic: .032" nominal thickness. **Brushed finish.**

This alloy contains 18% chromium and 8% nickel for superior resistance to corrosion. **Recommended for use in food processing plants, dairies, chemical plants, and other industrial, institutional, and commercial applications where corrosive atmospheres exist.**

Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide. **Packaged in protective film, with finish-matching screws.**

Variety of special plated finishes. **Paintable to match plastic plates.**

Can be silk-screened or engraved, and custom punched with over 300 opening styles.

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	United States
Application Sector	Residential/Commercial	Standard	CSA

Dimensions

Product Width US	2.75 in	Product Depth US	0.2 in
Product Height US	4.5 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Cutout	Television or Cable Lead-In	Thickness	0.032 in
--------	-----------------------------	-----------	----------

Number of Gangs	1
-----------------	---
