



Pass and Seymour
Louver Plate, One Gang Horizontal, 302/304 Stainless Steel Painted Light Almond
Part No. SS760LA



Smooth Metal Wall Plate 1-Gang Louver Horizontal 302/304 Stainless Steel Painted

Features & Benefits

Type 302/304 Stainless Steel, non-magnetic: .032" nominal thickness.

Brushed finish.

This alloy contains 18% chromium and 8% nickel for superior resistance to corrosion.

Recommended for use in food processing plants, dairies, chemical plants, and other industrial, institutional, and commercial applications where corrosive atmospheres exist.

Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide.

Packaged in protective film, with finish-matching screws.

Variety of special plated finishes.

Paintable to match plastic plates.

Can be silk-screened or engraved, and custom punched with over 300 opening styles.

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	United States
--------------	----------------	-------------------	---------------

Application Sector	Residential/Commercial	Standard	CSA
--------------------	------------------------	----------	-----

Dimensions

Product Width US	2.75 in	Product Depth US	0.2 in
------------------	---------	------------------	--------

Product Height US	4.5 in
-------------------	--------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	143223	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Cutout	Louver	Thickness	0.032 in
--------	--------	-----------	----------

Number of Gangs

1

Orientation

Horizontal
