



Pass and Seymour  
**Louver Plate, One Gang Vertical, 302/304 Stainless Steel Painted White**  
Part No. SS771W



Smooth Metal Wall Plate, 1-Gang Louver Vertical, 302/304 Stainless Steel Painted

Features & Benefits

Type 302/304 Stainless Steel, non-magnetic: .032" nominal thickness.	Brushed finish.
This alloy contains 18% chromium and 8% nickel for superior resistance to corrosion.	Recommended for use in food processing plants, dairies, chemical plants, and other industrial, institutional, and commercial applications where corrosive atmospheres exist.
Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide.	Packaged in protective film, with finish-matching screws.
Variety of special plated finishes.	Paintable to match plastic plates.
Can be silk-screened or engraved, and custom punched with over 300 opening styles.	

Specifications

General Info			
Product Line	Pass & Seymour	Country Of Origin	United States
Application Sector	Residential/Commercial	Standard	CSA
Dimensions			
Product Width US	2.75 in	Product Depth US	0.2 in
Product Height US	4.5 in		
Listing Agencies / 3rd Party Agencies			
cULus Listed	Yes		
Technical Information			
Cutout	Louver	Thickness	0.032 in

Number of Gangs	1	Orientation	Vertical
-----------------	---	-------------	----------