


Smooth Metal Wall Plate, 2-Gang Duplex, 302/304 Stainless Steel



Features & Benefits

Type 302/304 Stainless Steel, non-magnetic: .032" nominal thickness.

Brushed finish.

This alloy contains 18% chromium and 8% nickel for superior resistance to corrosion.

Recommended for use in food processing plants, dairies, chemical plants, and other industrial, institutional, and commercial applications where corrosive atmospheres exist.

Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide.

Packaged in protective film, with finish-matching screws.

Variety of special plated finishes.

Paintable to match plastic plates.

Can be silk-screened or engraved, and custom punched with over 300 opening styles.

Specifications

General Info

Product Line	Pass & Seymour	Color	Stainless Steel
Finish	Metallic	UPC Number	785007129342
Country Of Origin	United States	Wall Plate Size	Standard Size
Wall Plate Type	Duplex Receptacle	Application Sector	Commercial, Residential
Standard	CSA	Warranty Type	1-Year Limited Warranty
Type	Wall Plate		

Dimensions

Product Width US	4.56 in	Product Depth US	0.2 in
------------------	---------	------------------	--------

Product Height US	4.5 in		
Listing Agencies / 3rd Party Agencies			
cULus Listed	Yes		
Additional Information			
Product Environmental Profile	Yes		
Technical Information			
Thickness	0.032 in	Number of Gangs	2
Indoor/Outdoor	Indoor	Mounting Type	Strap Mounted
Orientation	Vertical		