



Pass and Seymour
Combination Openings, 1 Duplex Receptacle and 1 Decorator, Two Gang, 302/304 Stainless Steel
Part No. SS826



2-Gang Smooth Metal Wall Plate with 1 Duplex Receptacle and 1 Decorator, 302/304 Stainless Steel

Features & Benefits

Type 302/304 Stainless Steel, non-magnetic: .032" nominal thickness.

Recommended for use in food processing plants, dairies, chemical plants, and other industrial, institutional, and commercial applications where corrosive atmospheres exist.

Packaged in protective film, with finish-matching screws.

Can be silk-screened or engraved, and custom punched with over 300 opening styles.

This alloy contains 18% chromium and 8% nickel for superior resistance to corrosion.

Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide.

Paintable to match plastic plates.

Specifications

General Info

Product Line	Pass & Seymour	Color	Stainless Steel
Country Of Origin	United States	Application Sector	Residential/Commercial
Standard	CSA		

Dimensions

Product Width US	4.56 in	Product Depth US	0.2 in
Product Height US	4.5 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Cutout	Receptacle and Decorator	Thickness	0.032 in
Number of Gangs	2		