



Double Weave, Standard length, Split Lace, Offset Eye. Cable Diameter - 0.750-0.990", Mesh Length - 13", Break Strength - 3,000 lbs.

## Features & Benefits

Slack grips are reusable grips used for pulling slack in underground cable preparatory to final placement.

They may also be used for cable removal. Slack grips feature an offset eye for easy attachment to the pulling line.

Mesh Length: 13

## Specifications

### General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Construction	Support and Strain Relief Grips, Various Types of Pulling	Application Sector	Industrial
Standard	UL/CSA Approval (consult factory)		

### Technical Information

Maximum Cable Range	0.75 in	Minimum Cable Range	0.99 in
Capacity	Various Cable Diameter Ranges	Mounting	Consult the Factory for Mounting Recommendations
Load	Approx. Break Strength: 3000		