



Ortronics
SWING-OUT WALL MOUNT CABINETS - 12RU - Plexiglass Door
Part No. SWM12RUPL-26-26



The Swing-Out Wall-Mount (SWM) and Swing-Out Wall-Mount Reinforced SWMR Series wall-mount cabinets provide a convenient and easy-to use solution for edge, IoT, PoE and small network applications. The small form factor cabinets are 28 in deep for medium to large network equipment. The cabinets are made of rugged welded steel and feature locking doors for PCI compliance in retail applications. The hinged, swing-out middle section provides easy access to the rear of mounted equipment. The SWMR series feature heavy duty latch and hinges to accommodate heavier weight loads. The SWM and SWMR series cabinets are perfect for secure networks, small data closets, retail, educational, edge computing, and all areas where floor space is at a premium.

The Legrand SWM Series wall mount cabinets are available in 12, 18 & 26 RU options and either solid, perforated or plexi doors.

Features & Benefits

UL2416 load rated	PCI Compliant
Full swing handle	Reversible hinged solid front locking door
Vented sides with mounting locations for optional cooling fans	Reversible rails for network or server configurability
12-24 threaded and square punched mounting holes	Cable knockouts at top and bottom of fixed rear pan
Large cutout in rear pan for access to wall	2 reversible mounting rails
2 front door lock keys	8 cable management rings
Owner's manual	

Specifications

General Info

Product Line	Ortronics	UPC Number	662875015376
Country Of Origin	Mexico	Application Sector	Commercial
Type	Enclosure		

Dimensions

Product Width US	26.0 in	Product Depth US	28.0 in
Product Height US	25.0 in		

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Static Load Capacity	125 lb
----------------------	--------
