



The Swing-Out Wall-Mount (SWM) and Swing-Out Wall-Mount Reinforced SWMR Series wall-mount cabinets provide a convenient and easy-to-use solution for edge, IoT, PoE and small network applications. The small form factor cabinets are 28 in deep for medium to large network equipment. The cabinets are made of rugged welded steel and feature locking doors for PCI compliance in retail applications. The hinged, swing-out middle section provides easy access to the rear of mounted equipment. The SWMR series feature heavy duty latch and hinges to accommodate heavier weight loads. The SWM and SWMR series cabinets are perfect for secure networks, small data closets, retail, educational, edge computing, and all areas where floor space is at a premium.

The Legrand SWM Series wall mount cabinets are available in 12, 18 & 26 RU options and either solid, perforated or plexi doors.

## Features & Benefits

|  |  |
|--|--|
| UL2416 load rated  | PCI Compliant  |
| Full swing handle  | Reversible hinged solid front locking door             |
| Vented sides with mounting locations for optional cooling fans | Reversible rails for network or server configurability |
| 12-24 threaded and square punched mounting holes               | Cable knockouts at top and bottom of fixed rear pan    |
| Large cutout in rear pan for access to wall                    | 2 reversible mounting rails                            |
| 2 front door lock keys   | 8 cable management rings                               |
| Owner's manual   |  |

## Specifications

### General Info

|                   |           |                    |              |
|-------------------|-----------|--------------------|--------------|
| Product Line      | Ortronics | UPC Number         | 662875015697 |
| Country Of Origin | Mexico    | Application Sector | Commercial   |
| Type              | Enclosure |                    |              |

---

Dimensions

---

|                  |         |                  |         |
|------------------|---------|------------------|---------|
| Product Width US | 26.0 in | Product Depth US | 26.0 in |
|------------------|---------|------------------|---------|

---

|                   |          |
|-------------------|----------|
| Product Height US | 45.92 in |
|-------------------|----------|

---

Additional Information

---

|                 |     |
|-----------------|-----|
| RoHS Conformant | Yes |
|-----------------|-----|

---

Technical Information

---

|                      |        |
|----------------------|--------|
| Static Load Capacity | 200 lb |
|----------------------|--------|

---