



Pass and Seymour

**Discontinued - Trademaster CFL/LED/Incandescent Single Pole/3-Way Toggle Dimmer, Ivory | Sub TSDCL303PI**

Part No. TDCL453PI



Works with select dimmable CFL/LED or incandescent lighting loads and features a sleek, sculpted ergonomic design for smooth, easy operation and precise control. The TDCL453P is convenient to operate with a standard ON/OFF toggle switch and separate dimming wheel for precise dimming control. Use specific suffix for color: W- white, BK- black, LA- light almond, I- ivory and no suffix for brown.

## Features & Benefits

Tough, impact-resistant thermoplastic housing.

Power-failure memory.

Superior heat management: no time wasting break off tabs.

Exclusive, screw-pressure-plate back wire terminals eliminates wire nuts.

Preset, Single Pole/3-Way

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Rating: 450W LED & CFL: 700W Incandescent: 120VAC 60Hz.

## Specifications

### General Info

Product Line	Pass & Seymour	Replaced by Part Number	TSDCL303PI
Color	Ivory	Country Of Origin	China
Application Sector	Residential	Standard	RoHS, CSA Listed, UL Listed, cULus
Type	Dimmer		

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

### Technical Information

Frequency Rating	120VAC 60 Hz	Connection	Screw Terminals
Amperage	1.6 A	Wattage	450 W
Voltage	120.0 V	Load	LED, CFL, Incandescent

---

Environmental Conditions	Humidity: Less than 95% non condensing
--------------------------	---

---