



Features & Benefits

Tough, impact-resistant thermoplastic housing.

Power-failure memory.

Superior heat management: no time wasting break off tabs.

Exclusive, screw-pressure-plate back wire terminals eliminates wire nuts.

Preset, Single Pole/3-Way

For covering patents, see www.legrand.us/patents.

Rating: 450W LED & CFL: 700W Incandescent: 120VAC 60Hz.

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	TSDCL303PLA
Color	Light Almond	Country Of Origin	China
Application Sector	Residential	Standard	RoHS, CSA Listed, UL Listed, cULus
Type	Dimmer		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Frequency Rating	120VAC 60 Hz	Connection	Screw Terminals
Amperage	1.6 A	Wattage	450 W
Voltage	120.0 V	Load	Incandescent, LED, CFL

Environmental Conditions	Humidity: Less than 95% non condensing
--------------------------	--