



Pass and Seymour

TradeMaster Toggle De-Hummer Fan Speed Control, Brown
Part No. TDDH163P

TradeMaster Toggle De-Hummer Fan Speed Control 120V 1.6 amp specially designed capacitive circuitry to virtually eliminate fan motor hum.



Features & Benefits

Tough, impact-resistant thermoplastic housing.

Matches appearance of standard P&S toggle switch.

Uses conventional 3-way wiring when used in conjunction with a 3-way switch.

Specially designed capacitive circuitry to virtually eliminate fan motor hum.

Specifications

General Info

Color	Brown	UPC Number	785007016055
Country Of Origin	China	Product Line	Pass & Seymour
Application Sector	Residential/Commercial	Standard	cULus, RoHS

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Voltage	120 V	Connection	Screw Terminals
Frequency Rating	120VAC 60Hz Hz	Environmental Conditions	Humidity: Less than 95% non condensing