



## Features & Benefits

Tough, impact-resistant thermoplastic housing.

Matches appearance of standard P&S toggle switch.

Uses conventional 3-way wiring when used in conjunction with a 3-way switch.

Specially designed capacitive circuitry to virtually eliminate fan motor "hum".

## Specifications

### General Info

Product Line	Pass & Seymour	Replaced by Part Number	TSDDH163PW
Color	White	Country Of Origin	China
Application Sector	Residential/Commercial	Standard	cULus, RoHS

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

### Technical Information

Frequency Rating	120VAC 60 Hz	Connection	Screw Terminals
Amperage	1.6 A	Voltage	120.0 V
Environmental Conditions	Humidity: Less than 95% non condensing		