



Features & Benefits

Tough, impact-resistant thermoplastic housing.

Power-failure memory.

Superior heat management: no time wasting break off tabs.

Exclusive, screw-pressure-plate back wire terminals eliminates wire nuts.

Preset, Single Pole/3-Way, 120V 1100VA

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	TSDLV1103PI
Color	Ivory	Country Of Origin	China
Application Sector	Residential/Commercial	Standard	cULus, RoHS
Type	Dimmer		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Frequency Rating	120VAC 60 Hz	Connection	Screw Terminals
Voltage	1100.0 V	Load	Low Voltage

Environmental Conditions Humidity: Less than 95% non
condensing
