



Ortronics  
**Clarity 5E Angled TracJack, T568A/B, 45 degree, Dark Yellow**  
Part No. TJ5E45-44



Clarity TracJacks are a front loading solution designed for the workstation. Larger module size provides better visibility and more area to lace and terminate cables.

## Features & Benefits

Easy to follow universal wiring label: Quick, user-friendly, eliminates confusion.

Front removable: Less intrusive access for adds, moves, changes.

Standard TracJack footprint: Fits in all Tracjack faceplates and housings.

Icon compatible, with C6 Marking on jack face: Supports 606 designation requirements.

RoHS compliant: Lead free.

Center tuned design: Transparent interface with Clarity6 cords.

Easy lace IDC housing: Reduces wiring time.

## Specifications

### General Info

|                    |                        |                   |             |
|--------------------|------------------------|-------------------|-------------|
| Product Line       | Ortronics              | Color             | Dark Yellow |
| UPC Number         | 662875480709           | Country Of Origin | Mexico      |
| Application Sector | Commercial, Industrial | Standard          | UL Standard |
| Warranty Type      | 5-Year                 | Type              | Jack        |

### Dimensions

|                   |         |                  |        |
|-------------------|---------|------------------|--------|
| Product Width US  | 0.73 in | Product Depth US | 1.1 in |
| Product Height US | 0.92 in |                  |        |

### Additional Information

|                |     |
|----------------|-----|
| RoHS Compliant | Yes |
|----------------|-----|

Technical Information

|                |        |                   |         |
|----------------|--------|-------------------|---------|
| Wire Gauge     | 22 AWG | Termination Style | 110     |
| Connector Type | RJ-45  | Impedance         | 100 Ohm |