



Ortronics
Clarity 10G TracJack, T568A/B, 180 degree, Wiremold Gray
Part No. TJ610-68



Clarity 10G TracJack, ETL tested as part of 100-meter 10 Gig channel solution. Front-loading and front removable. Universal T568A/B wiring label and tapered wiring towers simplify termination. Center tuned with synchronized reactance to Clarity 10G patch cords for optimum performance with minimized internal and alien crosstalk.

Features & Benefits

Recessed design: Provides a more flush aesthetic look.

Meets Category 6A component standard: Ensures standards compliance.

Center tuned synchronized reactance design: Transparent interface with Clarity 10G cords.

Easy lace IDC housing: Reduces wiring time.

Easy to follow universal wiring label: Quick and user-friendly, eliminates confusion.

Front removable: Less intrusive access for adds, moves, changes

Standard TracJack footprint: Fits in all TracJack faceplates and housings.

Icon compatible, 10G Marking on jack face: Supports 606 designation requirements.

Specifications

General Info

Product Line	Ortronics	Color	Gray
UPC Number	662875590712	Country Of Origin	Mexico
Application Sector	Commercial, Industrial	Standard	UL Standard
Warranty Type	5-Year	Type	Jack

Dimensions

Product Width US	0.73 in	Product Depth US	1.1 in
Product Height US	0.92 in		

Additional Information

RoHS Compliant	Yes	Product Environmental Profile	Yes
----------------	-----	-------------------------------	-----

Technical Information

Wire Gauge	22-24 AWG	Termination Style	110
------------	-----------	-------------------	-----

Connector Type	RJ-45	Impedance	100 Ohm
----------------	-------	-----------	---------

Connectivity Footprint	TracJack
------------------------	----------
