



Pass and Seymour  
**Tamper-Resistant Floor Box Brass Cover**  
Part No. TM1542TRFM



Low-Profile Brass Cover requires minimum 3/8-inch hardwood floor thickness. Includes 885 15A, 125A Decorator Duplex receptacle and will accept any decorator device.

## Features & Benefits

Tamper-Resistant shutters let plugs in, keep other things out.

Standard Decorator opening that accepts GFCI, TVSS, DataCom, or other Decorator devices.

Meets UL514(c) scrub water exclusion test.

Simple mounting box, fits into a 4 3/4 inch hole and mounts with 3 screws included.

UL and cUL Listed.

Made in USA.

Durable construction, impact, and scratch resistant PVC construction.

Auto/Clamps and knockouts on both sides of box.

Threaded device mounting holes.

Ready for low-voltage wiring, drill guides on underside of cover.

Captive screws on TM1542 Series -- screws will not be lost -- new.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Brass
Country Of Origin	United States	Application Sector	Residential/Commercial
Standard	UL listed		

### Dimensions

Cubic Capacity	38 cu in
----------------	----------

### Listing Agencies / 3rd Party Agencies

---

cULus Listed	Yes
--------------	-----

---

Technical Information

---

Is Tamper-Resistant	Yes	Number of Outlets	1
---------------------	-----	-------------------	---

---