



radiant Collection
radiant® 15A Tamper-Resistant USB Outlet, Nickel
Part No. TM826USBNICC6



Get a full battery for your phones, tablets and more with the convenience of built-in charging. This tamper-resistant USB outlet includes two USB Type-A connections and replaces traditional outlets in as little as ten minutes, providing easy-to-access charging without needing bulky adapters or sacrificing your plugs. Also features the sleek, clean lines of radiant® for a sophisticated look. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Provides convenient built-in charging, without sacrificing plugs or requiring a bulky adapter.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

All Legrand USB Outlets are manufactured through high-quality design, sourcing and production, and backed by a Lifetime Warranty.

Replaces a traditional outlet easily, in as little as 10 minutes, with features like scalloped cover design and posted side-wire terminal screws for faster installation.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Specifications

General Info

| | | | |
|-----------------------|---|-------------------|-------------------------|
| Product Line | Pass & Seymour | Color | Nickel |
| Finish | Frosted | Country Of Origin | China |
| Number of Receptacles | 2 | Features | USB-A Charging |
| Outlet Type | Indoor, Residential, Tamper-Resistant, USB-Charging | Warranty Type | 1-Year Limited Warranty |
| Type | Outlet | | |

Dimensions

| | | | |
|------------------|---------|------------------|---------|
| Product Width US | 1.69 in | Product Depth US | 1.35 in |
|------------------|---------|------------------|---------|

| | |
|-------------------|---------|
| Product Height US | 4.18 in |
|-------------------|---------|

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Additional Information

| | |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

Technical Information

| | | | |
|---------------------|-----|--------------|-------|
| Is Tamper-Resistant | Yes | USB Amperage | 3.1 A |
|---------------------|-----|--------------|-------|

| | | | |
|----------------|---|------------------|------|
| Number of USBs | 2 | USB Power Output | 15 W |
|----------------|---|------------------|------|

| | | | |
|----------|------|-----------------|-------------|
| Amperage | 15 A | Number of Poles | Double Pole |
|----------|------|-----------------|-------------|

| | | | |
|----------------|--------|-------------------------|-------|
| Indoor/Outdoor | Indoor | NEMA Configuration Code | 5-15R |
|----------------|--------|-------------------------|-------|

| | | | |
|---------------|-----|---------|---------|
| Mounting Type | Box | Voltage | 125.0 V |
|---------------|-----|---------|---------|

| | |
|--------------------------|---|
| Environmental Conditions | 95% (relative humidity, non-condensing) |
|--------------------------|---|
