



radiant Collection
radiant® 3.1A USB Outlet, Type A, 15A, Tamper-Resistant, White
Part No. TM826USBWPW2CCV4



Get a full battery for your phones, tablets and more with the convenience of built-in charging. This tamper-resistant USB outlet includes two USB Type-A connections and replaces traditional outlets in as little as ten minutes, providing easy-to-access charging without needing bulky adapters or sacrificing your plugs. Also features the sleek, clean lines of radiant® for a sophisticated look. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Provides convenient built-in charging, without sacrificing plugs or requiring a bulky adapter.	All Legrand USB Outlets are manufactured through high-quality design, sourcing and production, and backed by a Lifetime Warranty.
Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.	Replaces a traditional outlet easily, in as little as 10 minutes, with features like scalloped cover design and posted side-wire terminal screws for faster installation.
More color options available to fit any style, including finishes to match current hardware and lighting trends.	Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Satin	UPC Number	785007207460
Country Of Origin	Vietnam	Number of Receptacles	2
Features	USB-A Charging	Outlet Type	Tamper-Resistant, USB-Charging
Application Sector	Hospitality, Residential	Wall Plate Included	Yes
Warranty Type	Limited Lifetime Warranty		

Dimensions

Product Width US	1.69 in	Product Depth US	1.35 in
Product Height US	4.18 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E140596	cULus Listed	Yes
---------------------	---------	--------------	-----

Technical Information

Is Tamper-Resistant	Yes	Connection Location	Back and Side
USB Wattage	15 W	USB Amperage	3.1 A
Number of USBs	2	Number of Wires	3
Amperage	15 A	Number of Poles	Double Pole
Indoor/Outdoor	Indoor	NEMA Configuration Code	5-15R
Mounting Type	Box	Wire Connection Type	Internal Pressure Plates, Screw Terminals
Voltage	5.0 V	Environmental Conditions	95% (relative humidity, non- condensing)