



Deco Combo 3-Way Switch & Pilot Light, White

## Features & Benefits

Impact-resistant face and body.

Fully rounded back body protects wires from being damaged by sharp edges.

Clear identification of circuits.

External screw-pressure-plate back and side wired. Accepts #12 and #14 AWG.

Ground screw position under the end of the strap minimizes the risk of contact.

Full wraparound metal strap with lock-in tabs.

Patented split circuit tab -- easily accessible, and can be reinstalled without a tool.

Unique "Up/Down" switches match the look and feel of standard Decorator switches.

Largest breadth of 15 amp offering.

All screws are tri-drive.

Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Country Of Origin	China	Application Sector	Residential/Commercial
Standard	UL 20	Type	Combination

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

### Technical Information

Amperage	15 A
----------	------