



radiant Collection
radiant® 15A Single-Pole Switch with Locator Light, Ivory
Part No. TM870ISLCC10



Ideal for spaces like bedrooms and baths, this switch provides on/off control from a single location and includes a small, built-in light to help you locate it in the dark. Part of the radiant® Collection, it also features clean lines and smooth paddle action for a sophisticated touch. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

For use with incandescent lights/bulbs only.

Locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark.

Features durable, high-impact resistant thermoplastic construction.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Replaces any standard switch with ease, in as little as 10 minutes.

Uses a paddle switch for smoother control with a low-profile aesthetic.

Designed to install easily with a narrower back body and captivated mounting screws.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Finish	Matte	UPC Number	785007856446
Country Of Origin	China	Features	Locator Light
Switch Type	Paddle	Number of Switches	1
Application Sector	Commercial, Residential	Warranty Type	1-Year Limited Warranty
Type	Switch		

Dimensions

Product Width US	1.43 in	Product Depth US	1.27 in
------------------	---------	------------------	---------

Product Height US 4.19 in

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

Contact Rating	15 Amp, 120/125 VAC	Number of Gangs	1
----------------	---------------------	-----------------	---

Amperage	15 A	Number of Poles	Single Pole
----------	------	-----------------	-------------

Wire Size	#14 - #10 AWG	Indoor/Outdoor	Indoor
-----------	---------------	----------------	--------

Mounting Type	Box
---------------	-----
