



radiant Collection
radiant® 15A 3-Way Switch, Nickel
Part No. TM873NICC10



Allowing control of a light or fixture from two separately located switches, the radiant® 3-Way Switch upgrades your space with clean lines and smooth paddle action for a sophisticated touch. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Replaces any standard switch with ease, in as little as 10 minutes

Uses a paddle switch for smoother control with a low-profile aesthetic

Features durable, high-impact resistant thermoplastic construction

Designed to install easily with a narrower back body and captivated mounting screws

More color options available to fit any style, including finishes to match current hardware and lighting trends

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection

Specifications

General Info

Product Line	Pass & Seymour	Color	Nickel
Finish	Metallic	UPC Number	785007021028
Country Of Origin	China	Switch Type	Paddle
Number of Switches	1	Application Sector	Commercial, Residential
Standard	CSA Listed, UL Listed	Warranty Type	1-Year Limited Warranty
Type	Switch		

Dimensions

Product Width US	1.43 in	Product Depth US	1.27 in
------------------	---------	------------------	---------

Product Height US	4.19 in
-------------------	---------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Operating Cycles	50000	Contact Rating	15 Amp, 120/125 VAC
Number of Gangs	1	Amperage	15 A
Number of Poles	3-Way, Single Pole	Wire Size	#14 - #10 AWG
Mounting Type	Box	Environmental Conditions	UL94 V2