



radiant Collection  
radiant® 15A 3-Way Switch, Nickel  
Part No. TM873NICC10



Allowing control of a light or fixture from two separately located switches, the radiant® 3-Way Switch upgrades your space with clean lines and smooth paddle action for a sophisticated touch. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

## Features & Benefits

Replaces any standard switch with ease, in as little as 10 minutes

Uses a paddle switch for smoother control with a low-profile aesthetic

Features durable, high-impact resistant thermoplastic construction

Designed to install easily with a narrower back body and captivated mounting screws

More color options available to fit any style, including finishes to match current hardware and lighting trends

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection

## Specifications

### General Info

|                    |                       |                    |                         |
|--------------------|-----------------------|--------------------|-------------------------|
| Product Line       | Pass & Seymour        | Color              | Nickel                  |
| Country Of Origin  | China                 | Switch Type        | Paddle                  |
| Number of Switches | 1                     | Application Sector | Residential             |
| Standard           | CSA Listed, UL Listed | Warranty Type      | 1-Year Limited Warranty |

### Dimensions

|                   |         |                  |         |
|-------------------|---------|------------------|---------|
| Product Width US  | 1.43 in | Product Depth US | 1.27 in |
| Product Height US | 4.19 in |                  |         |

### Listing Agencies / 3rd Party Agencies

---

|              |     |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

---

### Additional Information

---

|                               |     |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

---

### Technical Information

---

|                  |       |                |      |
|------------------|-------|----------------|------|
| Operating Cycles | 50000 | Contact Rating | 120V |
|------------------|-------|----------------|------|

---

|                 |   |          |      |
|-----------------|---|----------|------|
| Number of Gangs | 1 | Amperage | 15 A |
|-----------------|---|----------|------|

---

|                 |                    |               |     |
|-----------------|--------------------|---------------|-----|
| Number of Poles | 3-Way, Single Pole | Mounting Type | Box |
|-----------------|--------------------|---------------|-----|

---

|         |           |                          |         |
|---------|-----------|--------------------------|---------|
| Voltage | 120/277 V | Environmental Conditions | UL94 V2 |
|---------|-----------|--------------------------|---------|

---