



Pass and Seymour
Discontinued - Tamper-Resistant Single Receptacle with 3.1A USB Charger, Ivory
Part No. TM88USBICC6



Features & Benefits

Classic duplex style matches traditional devices like 3232s	2 USB A-Type charging ports 3.1A total charging capacity (simultaneously charges 2 tablets)
Compatible with USB 2.0 & 3.0 devices	Efficient 5Vdc transformer
Side and back-wire terminals	Tamper-Resistant receptacle to meet latest NEC: code requirements
Self-grounding clip standard on all Commercial and Hospital Grade models	Slim 1.3-inch depth
cULus listed	

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Country Of Origin	China		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Is Tamper-Resistant	Yes	USB Amperage	3.1 A
Number of USBs	2	USB Power Output	15 W

Amperage

15 A
