



Pass and Seymour
TradeMaster® 2-Gang Nylon Wall Plate, 2 Decorator Openings, Orange
Part No. TP262OR



The TradeMaster® thermoplastic 2-gang decorator wall plate provides maximum durability in plastic wall plates. Self-extinguishing nylon construction makes these wall plates virtually unbreakable. They are 3/16 of an inch higher and wider than typical plastic wall plates - not enough to be apparent to the eye, but the extra size cuts cost by reducing dry wall rework.

Features & Benefits

Molded of rugged, practically indestructible self-extinguishing nylon. ('TP' series only)

Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond

Nominal thickness, .070 inch

Available in 'TP' series, extra 3/16 inch width and height than Standard size plates: and 'TPJ' series, extra 3/16 inch width and height than Junior-Jumbo size plates

Preferred for hospital, industrial, institutional, and other high-abuse applications

Specifications

General Info

Product Line	Pass & Seymour	Color	Orange
Finish	Matte	UPC Number	785007276275
Country Of Origin	United States	Construction	Plastic
Wall Plate Size	Standard Size	Wall Plate Type	Decorator
Application Sector	Commercial, Residential	Standard	CSA, UL514
Warranty Type	1-Year Limited Warranty	Type	Wall Plate

Dimensions

Product Width US	4.75 in	Product Depth US	0.25 in
------------------	---------	------------------	---------

Product Height US	4.6875 in
-------------------	-----------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	143222	cULus Listed	Yes
---------------------	--------	--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Thickness	0.07 in	Number of Gangs	2
Indoor/Outdoor	Indoor	Mounting Type	Box Mounted
Orientation	Vertical		