



Pass and Seymour
Thermoplastic One-Gang Decorator Wall Plate, Ivory
Part No. TP26I



The TradeMaster thermoplastic 1-gang decorator wall plate provides maximum durability in plastic wall plates. Self-extinguishing nylon construction makes these wall plates virtually unbreakable. They are 3/16 of an inch higher and wider than typical plastic wall plates - not enough to be apparent to the eye, but the extra size cuts cost by reducing dry wall rework.

Features & Benefits

Molded of rugged, practically indestructible self-extinguishing nylon. ('TP' series only)

Available in 'TP' series, extra 3/16 inch width and height than Standard size plates: and 'TPJ' series, extra 3/16 inch width and height than Junior-Jumbo size plates

Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond

Preferred for hospital, industrial, institutional, and other high-abuse applications

Nominal thickness, .07 inch

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Country Of Origin	United States	Wall Plate Type	Dimmer/Switch, Outlet
Application Sector	Residential/Commercial	Standard	CSA, UL514
Type	Wall Plate		

Dimensions

Product Width US	2.9375 in	Product Depth US	0.25 in
Product Height US	4.6875 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	143222	cULus Listed	Yes
---------------------	--------	--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Cutout	Decorator	Thickness	0.07 in
--------	-----------	-----------	---------

Number of Gangs	1	Mounting Type	Exposed Screws
-----------------	---	---------------	----------------