



Pass and Seymour
TradeMaster® 1-Gang Nylon Wall Plate, 1 Decorator Opening, Light Almond
Part No. TP26LA



The TradeMaster thermoplastic 1-gang decorator wall plate provides maximum durability in plastic wall plates. Self-extinguishing nylon construction makes these wall plates virtually unbreakable. They are 3/16 of an inch higher and wider than typical plastic wall plates - not enough to be apparent to the eye, but the extra size cuts cost by reducing dry wall rework.

Features & Benefits

Molded of rugged, practically indestructible self-extinguishing nylon. ('TP' series only)

Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond

Nominal thickness, .07 inch

Available in 'TP' series, extra 3/16 inch width and height than Standard size plates: and 'TPJ' series, extra 3/16 inch width and height than Junior-Jumbo size plates

Preferred for hospital, industrial, institutional, and other high-abuse applications

Specifications

General Info

Product Line	Pass & Seymour	Color	Light Almond
Finish	Matte	UPC Number	785007275094
Country Of Origin	United States	Construction	Plastic
Wall Plate Size	Standard Size	Wall Plate Type	Decorator
Application Sector	Commercial, Residential	Standard	CSA, UL514
Warranty Type	1-Year Limited Warranty	Type	Wall Plate

Dimensions

Product Width US	2.9375 in	Product Depth US	0.25 in
------------------	-----------	------------------	---------

Product Height US	4.6875 in
-------------------	-----------

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes
------------	-----	--------------	-----

Additional Information

RoHS Compliant	Yes	Product Environmental Profile	Yes
----------------	-----	-------------------------------	-----

Technical Information

Thickness	0.07 in	Number of Gangs	1
Indoor/Outdoor	Indoor	Mounting Type	Box Mounted
Orientation	Vertical		