



Pass and Seymour  
**TradeMaster® 3-Gang Nylon Wall Plate, 2 Toggle Switch Openings, 1 Duplex Receptacle Opening, Brown**  
Part No. TP28



Trademaster Plate 3-Gang, 2-toggle, 1-duplex receptacle

## Features & Benefits

Molded of rugged, practically indestructible self-extinguishing nylon. ('TP' series only.)	High Impact resistant nylon face.
Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.	Preferred for hospital, industrial, institutional, and other high-abuse applications.
Nominal thickness, .070 inch.	

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Brown
Finish	Matte	UPC Number	785007275124
Country Of Origin	Mexico	Construction	Plastic
Wall Plate Size	Standard Size	Wall Plate Type	Combination, Duplex Receptacle, Toggle Switch
Application Sector	Commercial, Residential	Standard	CSA, UL514
Warranty Type	1-Year Limited Warranty	Type	Wall Plate

### Dimensions

Product Width US	6.563 in	Product Depth US	0.25 in
Product Height US	4.6875 in		

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	143222	cULus Listed	Yes
---------------------	--------	--------------	-----

### Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

### Technical Information

Thickness	0.07 in	Number of Gangs	3
-----------	---------	-----------------	---

Indoor/Outdoor	Indoor	Mounting Type	Box Mounted
Orientation	Vertical		