



Trademaster Plate 3-Gang, 2-toggle, 1-duplex receptacle

## Features & Benefits

Molded of rugged, practically indestructible self-extinguishing nylon. ('TP' series only.)

High Impact resistant nylon face.

Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.

Preferred for hospital, industrial, institutional, and other high-abuse applications.

Nominal thickness, .070 inch.

## Specifications

### General Info

|                    |                        |                 |                                    |
|--------------------|------------------------|-----------------|------------------------------------|
| Product Line       | Pass & Seymour         | Color           | Ivory                              |
| Country Of Origin  | Mexico                 | Wall Plate Type | Combination, Dimmer/Switch, Outlet |
| Application Sector | Residential/Commercial | Standard        | CSA, UL514                         |

### Dimensions

|                   |           |                  |         |
|-------------------|-----------|------------------|---------|
| Product Width US  | 6.563 in  | Product Depth US | 0.25 in |
| Product Height US | 4.6875 in |                  |         |

### Listing Agencies / 3rd Party Agencies

|                     |        |              |     |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 143222 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

### Additional Information

|                               |     |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

### Technical Information

---

|                 |                       |               |                |
|-----------------|-----------------------|---------------|----------------|
| Cutout          | Toggle and Receptacle | Thickness     | 0.07 in        |
| Number of Gangs | 3                     | Mounting Type | Exposed Screws |

---